

# USER INSTRUCTIONS

## CAUTION

**SUNLAMP--DANGER--ULTRAVIOLET RADIATION**  
**USE ONLY IN FIXTURE EQUIPPED WITH A TIMER**

**DANGER--ULTRAVIOLET RADIATION**

### FOLLOW INSTRUCTIONS

Avoid overexposure. As with natural sunlight, overexposure can cause eye and skin injury and allergic reactions. Repeated exposure may cause premature aging of the skin and skin cancer. **WEAR PROTECTIVE EYEWEAR; FAILURE TO MAY RESULT IN SEVERE BURNS OR LONG-TERM INJURY TO THE EYES.** Medications or cosmetics may increase your sensitivity to the ultraviolet radiation. Consult physician before using sunlamp if you are using medications or have a history of skin problems or believe yourself especially sensitive to sunlight. If you do not tan in the sun, you are unlikely to tan from the use of this product.

*The instructions accompanying the sunlamp product should ALWAYS be followed to avoid potential injury.*

**ALWAYS RETAIN THIS FORM FOR FUTURE REFERENCE AND LAMP COMPATIBILITY INFORMATION.**

<u>MODEL</u>	<u>COMPATIBLE WITH</u>	<u>LENGTH</u>	<u>WATTS</u>	<u>BASE</u>
SA18T8/AMAX	-- Sundash HFR by Voltarc® P/N26934	18"	20	Bi-Pin
F40/Shoulder Lamp Super Sun®	-- Philips CLEO Performance 40W	24"	40	Bi-Pin
SR59/BP Plus Super Sun® Reflector	-- Philips R-UVA 80W Philips TL 80W/09R R-UVA	59"	85	Bi-Pin
SS59/BP Super Sun® II	-- Wolff Diamond Sun S DSS59-T12-80W Wolff Bellarium S SA1-59-80W Wolff Velocity VEL 59-T12-80W Wolff System Accelerator ACC59-T12-80W Preheat Bipin Wolff System EverGlo 59"/80W Wolff System Body Scan X Plus; F59/80W Bipin; Preheat	59"	85	Bi-Pin
SS59/BP 2.6 Super Sun®	-- Wolff Crystal Sun S DA1-59-80W BiPin	59"	85	Bi-Pin
SS59/VHO 2.6 Super Sun®		59"	140	Bi-Pin
SS59/BP 3.5 Super Sun®	-- Cosmedico Goldarium S SA1-12-80W Sunfit Professional X 80W	59"	85	Bi-Pin
SS59/BP 5.5 Super Sun®	-- Light Sources F59T12-BL-BP/42 Wolff System EverGlo 59"/80W Voltarc F59T12-BL-BP/42	59"	85	Bi-Pin
SS59/BP/A-RAY	-- Philips TL 80W/09N UV-A	59"	85	Bi-Pin
SS59/BP/3.2	-- JK Soltron S 80W Cosmolux AS A1-12-80W Preheat Bi-pin Wolff System Diamond Sun DS59-T12-80W Preheat Bipin	59"	85	Bi-Pin
SS59/BP/PANTHER®	-- Cosmedico Hi-Tan Preheat Bi-pin 80W Radiance 7000 F59	59"	85	Bi-Pin
SS59/BP/PHOENIX®	-- Sunbronze F59T12-BL-BP/85 EuroSun S3 ES3-59-80W Cosmedico Hi-Tan Preheat Bi-pin 80W Radiance 7000 F59	59"	85	Bi-Pin
SS59/BP/PHOENIX® Extreme	-- Cosmedico Hi-Tan Preheat Bi-pin 80W Radiance 7000 F59	59"	85	Bi-Pin
SR59/BP/GEM-R	-- Sunfit RX 80W Professional	59"	85	Bi-Pin

**INTERLECTRIC  
CORPORATION**



1401 LEXINGTON AVENUE, WARREN, PA 16365

5/14/09

**Super Sun® Lamps**  
1-800-722-2184 (PA: 814-723-6061)